



Note:

No.	A	B	C
09	16.92	24.99	30.81

WITH ASSEMBLED HEX SCREW BOLTS

ELECTRICAL CHARACTERISTICS

Contact Current Rating: 3 Amperes.
 Dielectric Withstanding Voltage: AC 500V at sea level.
 Insulation Resistance: 1000 Megohms Min.
 Contact Resistance: 30 Milliohms Max.
 Operation Temperature: -55°C to +105°C.

Material

Contact: Copper Alloy.
 Insulator: PBT. [Select PA6T /LCP /PA9T]
 Shell: SPCC.
 Z-Piece: Fe.
 Screw: Copper Alloy.
 Rivet: Copper Alloy or Zinc.

