



Impedance	50Ω
Frequency range	0.1 GHz
VSWR (straight connectors)	≤ 1.22 typ
Insulation resistance	≥ 5 × 10 ¹⁰ MΩ
Center contact resistance	≤ 10.0 mΩ
Outer contact resistance	≤ 8.0 mΩ
Test voltage	1000V rms
Working voltage	500V rms
Insertion loss(dB)	≤ 0.1dB max/1530 typ

No.	DESCRIPTION	MATERIAL	FINISH
1	BODY	BRASS	NICKEL
2	CONTACT	BRASS	GOLD
3	INSULATOR	TEFLON	WHITE
4	FERRULE	BRASS	NICKEL

