



Impedance	50Ω
Frequency range	0-3 GHz
VSWR (straight connectors)	< 1.25 typ
Insulation resistance	$\geq 5 \times 10^3 \text{ M}\Omega$
Center contact resistance	< 10.0 mΩ
Outer contact resistance	< 5.0 mΩ
Test voltage	1000V rms
Working voltage	500 V rms
Insertion loss(dB)	< 0.1dB max./ Hz @ 1V

No.	DESCRIPTION	MATERIAL	FINISH
1	BODY	BRASS	NICKEL
2	CONTACT	BRASS	GOLD
3	INSULATOR	DELIN	WHITE
4	SHELL	BRASS	NICKEL