



Impedance	50 Ω
Frequency range	0.1 GHz
VSWR (straight connector)	≤ 1.22 (1σ)
Insulation resistance	≥ 5 × 10 <sup>11</sup> Ω
Center contact resistance	≤ 10 mΩ
Outer contact resistance	≤ 10 mΩ
Test voltage	1000V rms
Working voltage	300V rms
Installation (use only)	≤ 0.1dB max/100μ 192

No.	DESCRIPTION	MATERIAL	FINISH
1	BODY	BRASS	NICKEL
2	CONTACT	BRASS	GOLD
3	INSULATOR	TEFLON	WHITE
4	FERRULE	BRASS	NICKEL
5	SUPPORT	DELRIN	WHITE
6	NUT	BRASS	NICKEL

