




▽ DIP2 PITCH 2.54MMX7.62MM I.D.C. DIP PLUG
FOR PITCH 1.27MM CENTER FLAT RIBBON CABLE

MATERIAL & FINISH

*INSULATOR: PBT+GLASS FIBER UL 94V-0

*CONTACT: BRASS

*FINISH: GOLD-PLATED OVER NICKEL
SPECIFICATIONS

*CURRENT RATING: 1A AC,DC

*VOLTAGE RATING: 250V AC,DC

*TEMPERATURE RANGE: -40°C TO $+105^{\circ}\text{C}$

*CONTACT RESISTANCE: $20\text{M}\Omega$ MAX

*INSULATION RESISTANCE: $1,000\text{M}\Omega$ MIN

*WITHSTANDING VOLTAGE: 500V AC/MIN

PIN	DIM A	DIM B
16	17.78	25.58

DIMENSIONS:MM