



## SPECIFICATIONS

**Current Rating:** 3 Amp

**Insulation Resistance:** 1000M $\Omega$  Min

**Dielectric Withstanding:** 600V AC/DC

**Contact Resistance:** 20m $\Omega$  Max.

**Operating Temperature:** -40 $^{\circ}$ c to +105 $^{\circ}$ c

## MATERIALS

**Contact Material:** Phosphor Bronze

**Insulation Material:** Polyester, UL 94V-0  
P.B.T or Nylon-6T

**Contact Plating:** Full Gold, Full Tin, Selective Plated

**Standard:** Gold Flash all Over Nickel

**All materials must be RoHS compliant.**