



### SPECIFICATIONS

**Current Rating:** 3 Amperes  
**Insulation Resistance:** 1000MΩ Min  
**Dielectric Withstanding:** 600V AC/DC  
**Contact Resistance:** 20mΩ Max.  
**Operating Temperature:** -40°C to +105°C

### MATERIALS

**Contact Material:** Copper Alloy  
**Contact Plating:** Gold / Tin over Nickel  
**Insulator:** Glass Filled Polyester (UL 94V-0)  
 P.B.T or Nylon-6T  
**All materials must be RoHS compliant.**

| Terminal Code | Dimensions(mm) |      |      |
|---------------|----------------|------|------|
|               | A              | B    | C    |
| QB            | 10.80          | 5.80 | 2.50 |