



### SPECIFICATIONS

**Current Rating:** 3 Amperes  
**Insulation Resistance:** 1000MΩ Min  
**Dielectric Withstanding:** 600V AC/DC  
**Contact Resistance:** 20mΩ Max.  
**Operating Temperature:** -40°C to +105°C

### MATERIALS

**Contact Material:** Copper Alloy  
**Contact Plating:** Gold / Tin over Nickel  
**Insulator:** Glass Filled Polyester (UL 94V-0)  
 P.B.T or Nylon-6T  
**All materials must be RoHS compliant.**

Terminal Code	Dimensions(mm)		
	A	B	C
QB	10.80	5.80	2.50