



SPECIFICATIONS

Current Rating: 3 Amperes
Insulation Resistance: 1000M Ω Min
Dielectric Withstanding: 600V AC/DC
Contact Resistance: 20m Ω Max.
Operating Temperature: -40 $^{\circ}$ c to +105 $^{\circ}$ c

MATERIALS

Contact Material: Copper Alloy
Contact Plating: Gold / Tin over Nickel
Insulator: Glass Filled Polyester (UL 94V-0)
 P.B.T or Nylon-6T
All materials must be RoHS compliant.

Terminal Code	Dimensions(mm)		
	A	B	C
QB	10.80	5.80	2.50