




Datenblatt



Recommended P.C.Board Layout



SPECIFICATIONS

Current Rating: 3.0 A

Voltage Rating: 60V AC/DC

Contact Resistance: 4mΩ Max.

Insulator Resistance: 1000MΩ Min.

Operating Temperature: -40°C to +105°C

MATERIALS

Insulator: PPS UL94V-0, Black

Pin: Brass, Machined CuZn38Pb2

Clip: Beryllium Copper

* RoHS & REACH compliant.