





Datenblatt



Recommended P.C.Board Layout

SPECIFICATIONS

Current Rating: 3.0 A

Voltage Rating: 60V AC/DC

Contact Resistance: 4m Ω Max.

Insulator Resistance: 1000M Ω Min.

Operating Temperature: -40 $^{\circ}$ c to +105 $^{\circ}$ c

MATERIALS

Insulator: PPS UL94V-0, Black

Pin: Brass, Machined CuZn38Pb2

Clip: Beryllium Copper

* RoHS & REACH compliant.