



Specifications:

Current Rating:1.0 Amp  
 Contact resistance:30m Ohm Max. at 6V DC 0.3A  
 Insulator resistance:1000M ohm min. at 500V DC  
 Withstanding Voltage:500V AC/Minute  
 Operating Temperature Range:-40°~+105°C  
 Wire Size Flat Cable I.D.C: 1.27mm Pitch  
 AWG#28(standard 0.20mm) OR #30 (0.17mm).  
 Material And Finish  
 Insulator:PBT&Glass-fiber reinforced UL94V-0  
 Insulator Color:Black or Gray  
 Contact:Phosphor Bronze or Brass  
 Contact Plating:See Contact Plating Tab.  
 Note:(\*)Marked is Important DIM For QC.

1. CONTACT MATERIAL & SR OPTION:  
 WITH BUMP (NOSE):

"DC" BRASS WITH STRAIN RELIEF

3. CONTACT FINISH:  
 "S" SELECTIVE GOLD PLATED  
 4. INSULATOR COLOR:  
 "B" BLACK (STANDARD)

No.	A	B	C	D
16	25.00	17.78	19.05	3.80