



Specifications:

Current Rating:1.0 Amp
 Contact resistance:30m Ohm Max. at 6V DC 0.3A
 Insulator resistance:1000M ohm min. at 500V DC
 Withstanding Voltage:500V AC/Minute
 Operating Temperature Range:-40~+105°C
 Wire Size Flat Cable I.D.C: 1.27mm Pitch
 AWG#28(standard 0.20mm) OR #30 (0.17mm).
 Material And Finish
 Insulator:PBT&Glass-fiber reinforced UL94V-0
 Insulator Color:Black or Gray
 Contact:Phosphor Bronze or Brass
 Contact Plating:See Contact Plating Tab.
 Note:(*)Marked is Important DIM For QC.

1. CONTACT MATERIAL & SR OPTION:

WITH BUMP (NOSE):

"DC" BRASS WITH STRAIN RELIEF

3. CONTACT FINISH:

"S" SELECTIVE GOLD PLATED

4. INSULATOR COLOR:

"B" BLACK (STANDARD)

No.	A	B	C	D
20	30.08	22.86	24.13	3.80