



**SPECIFICATION:**

- 1, RATING 1A; 12VDC
- 2, OPERATING TEMPERATURE -40°C to +105°C

5	CRIMPING PATCH	Cu
4	SOLDERING PATCH	Cu
3	BODY	Cu
2	PLASTIC HANDLE	PE
1	DIELECTRIC	POM
ITEM	DESIGNATION	MATERIAL