


Datasheet


Item no. 1586431


V1_0617_02_EN












Plastic knop	Plating
Black	Black

Thread	
A	Plating
UNC4-40	Zink



SPECIFICATION
MATERIAL
Features

Material and finish
Zinc-die-cast,nickel plated

Temperature range
-40° to +120°

Cable diameter
4.0mm - 13.0mm

Attenuation factor
>40 dB between
30Mhz and 1Ghz

Requirements
VDE 0871,FCC 20780,
89/336/EU

Material
Zinc die-cast

Delivery includes

1	half-sheels	(2x)
2	knurledge screws	(2x)
3	screw	(1x)
4	half shells of strain relief	(8x)