








NOTES:

- ① Connector Meets Requirement OF DIN 41612
- ② Material:
 - 1.Housing : Glass-Filled PBT. Color: Grey, UL 94V-0
 - 2.Contact : Copper Alloy
- ③ Contact Tail Dimension(Thickness x Width x Length)(a=Length)(Option in Part Number)

T	:0.3±0.02 x 0.64±0.04 x 4±0.2
T2.5	:0.3±0.02 x 0.64±0.04 x 2.5±0.2
W5	:0.6±0.015 x 0.6±0.03-0.05 x 5±0.2
W7	:0.6±0.015 x 0.6±0.03-0.05 x 7.4±0.2
- ④ Contact Finish(Option in Part Number)

-1: 25µ" (0.63µm)Pd/Ni and 2µ"Gold Plating on Mating Area ,100µ"(2.54µm)Tin Plating on Tail Area, Flash Gold Plating on Non-mating Area,50µ" (1.27µm)Nickel Underplate All Over
-2: 12µ" (0.30µm)Pd/Ni and 2µ"Gold Plating on Mating Area ,100µ"(2.54µm)Tin Plating on Tail Area, Flash Gold Plating on Non-mating Area,50µ" (1.27µm)Nickel Underplate All Over
Blank: Flash Gold Plating on mating and non-mating Area, Tin Plating on Tail Area,Nickel Underplate All Over
- ⑤ Connector Printed with Part Number,and Batch Number



RoHS compliant