



Recommended PCB Hole Layout
Component Side
Scale 1:1



Recommended Hole Specifications
Section A-A
Scale 6:1

NOTES:

- ① Connector Meets Requirement OF DIN 41612
- ② Material:
 - 1.Housing : Glass-Filled PBT. Color: Grey, UL 94V-0
 - 2.Contact : Copper Alloy
- ③ Contact Tail Dimension(Thickness x Width x Length)

x=	T	: 0.3±0.02 x 0.64±0.04 x 4±0.2
	T2.5	: 0.3±0.02 x 0.64±0.04 x 2.5±0.2
	④ W5	: 0.6±0.015 x 0.6+0.03-0.05 x 5±0.2
	③ W7	: 0.6±0.015 x 0.6+0.03-0.05 x 7.4±0.2
- ④ Contact Finish(Option y in Part Number)

y=	-1:	25µ" (0.63µm)Pd/Ni and 2µ"Gold Plating on Mating Area ,100µ"(2.54um)Tin Plating on Tail Area, Flash Gold Plating on Non-mating Area,50 µ" (1.27µm)Nickel Underplate All Over
	-2:	12µ" (0.30µm)Pd/Ni and 2µ"Gold Plating on Mating Area ,100µ"(2.54um)Tin Plating on Tail Area, Flash Gold Plating on Non-mating Area,50 µ" (1.27µm)Nickel Underplate All Over
	Blank:	Flash Gold Plating on mating and non-mating Area, Tin Plating on Tail Area,Nickel Underplate All Over
- ⑤ Connector Printed with Part Number,and Batch Number

RoHS compliant