




Datasheet

Item no. 1586540

V1_0617_02_EN



PCB LAYOUT

CKT	A±0.20	B±0.20
28	35.56	33.02

MATERIAL:

Contact :
Phosphor Bronze thickness 0.15mm
Plating :
Contact Plating, Tin plated 60u"~80u"
(Lead free plating)
Insulator :PBT-4830 , UL 94V-0

SPECIFICATIONS:

Current Rating : 1A
Dielectric withstanding Voltage : 1000v RMS/minute
Insulator resistance : 5000 Megohms min.
Contact resistance : 20 milliohms initial
30 milliohms after test.
Operating temperatures : -55°c to 85°c
Insertion force : 340g(12 oz) max.per contact.
Withdrawal force : 80g(2.82 oz) min.per contact
Soldering temperature: +245°C , 5S max.

RoHS compliant
Unit: mm