




Rocker Switch (printing 0 / I)

Rating	UL CSA 6A 125V, 4A 250V AC VDE 10A 125V, 6A 250V AC	Mount Hole		Circuit Structure												
Contact R	50m ohm Max.	<table border="1"> <tr> <th>Thickness</th> <th>X</th> <th>Y</th> </tr> <tr> <td>0.75-1.25</td> <td>19.2-0.3</td> <td>13±0.1</td> </tr> <tr> <td>1.25-2</td> <td>19.4-0.3</td> <td>13±0.1</td> </tr> <tr> <td>2-3</td> <td>19.8-0.3</td> <td>13±0.1</td> </tr> </table>	Thickness	X	Y	0.75-1.25	19.2-0.3	13±0.1	1.25-2	19.4-0.3	13±0.1	2-3	19.8-0.3	13±0.1		
Thickness	X		Y													
0.75-1.25	19.2-0.3		13±0.1													
1.25-2	19.4-0.3	13±0.1														
2-3	19.8-0.3	13±0.1														
Insulation R	DC 500V 100M ohm Min.															
Dielectric Strength	AC 1500V 1 minute															
Circuit	4P DPST ON-OFF															



Unit: mm