




Datasheet

Item no. 1587561

V1_0817_01_en

Rocker Switch

Rating	10A 125V AC	Mounting Hole	Diagram
Contact Resistance	16A 125V AC,10A 250V AC (\$1).s	18 2	
	DC 500V 100M ohm Min.	Econo de la constante de la co	0
Dielectric Strength	AC 1500V 1 minute		SV DC O
Operation Temperature	-20°C~85°C	KH.	+-b i i
Switch Function	4P SPST ON-OFF with LED	18.6 - 0.1	




*Material

Frame: Nylon#66+33%GF, Black Actuator: Nylon#66, Black

Lens: Po

Terminal: Copper alloy, Silver plated



1821110	Yellow	Orange Clear	
1821109	Green	Green Clear White Clear	
1820949	Red		
SCI NO.	LED Color	Lens Color	

Unit: mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.