





# Push Switch

Rating	3A 125V, 1.5A 250V AC 	Mount Hole	Circuit Structure	
Contact R	50m ohm Max.		OFF	
Insulation R	DC 500V 100M ohm Min.			ON
Dielectric Strength	AC 1500V 1 minute			
Operating Temperature	-20°~85°			
Circuit	4P SPST ON-OFF (LED)			

LED Rating  
 Red: @20mA, If=2.0VDC  
 Amber: @20mA, If=2.1VDC  
 Green: @20mA, If=2.2VDC



Unit: mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.