












Push Pull Switch

		<p>BUTTON</p>	<p>ENCLOSURE</p>	<p>TERMINAL</p>
<p>10A 12V DC</p>	<p>10A 12V DC</p>	<p>A A3-5F-3A 25.5</p> 	<p>A 20.7mm</p> 	<p>0 1  .250" SQ</p>
<p>∅ 8.2</p>	<p>OFF ON</p> 	<p>B A3-5-3 13</p> 	<p>B 7.2mm</p> 	<p>0 6  SC M3</p>
		<p>C A3-5C-3B 19</p> 	<p>C 14.5mm</p> 	

Unit: mm