







Panel Switch

Rating	50A 12VDC Max.(Start Switch) 20A 12VDC (Toggle Switch) 20mA 12VDC (LED Indicator)	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-25°C~85°C		

Descriptions:

- Switch: 3P SPST ON-OFF (RED LED).
- Indicator: (RED LED).
- Push switch: A2-23B-07, 3P SPST (ON)-OFF (RED LED).
- Safety Cover: RED.
- Panel: Aluminum, Water Transfer Printed, Carbon.



Unit: mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.