




Key Switch

Rating	15A Max. 12VDC	Mounting Hole 	Circuit Diagram 
Contact Resistance	50M ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.	Thickness: 5.5mm max.	
Dielectric Strength	AC 1000V 1 minute		
Operation Temperature	-20°C~85°C		
Switch Function	4P ON - OFF - ON - momentarily ON turn left - Key IN - right - right EIN - AUS - EIN - Taster		



Unit: mm