


## Distributed by Conrad Electronic SE • Klaus-Conrad-Str. 1 • D-92240 Hirschau


## **Datasheet**


Item no. 1588005

V1\_0817\_01\_en

## Fuse block w/ 4P, with LED warning light










Unit: mm

Voltage (Max.)	32 VDC.	Mounting Hole	
Input Terminial Rating	#10-32 threaded studs (100A. max.)	<del></del>	
Output Terminial Rating	30A max per circuit.	238810	
Connection pad option available	Input wire size : #4-6 AWG.	48.0±1.0	
	Output wire size : #12-16 AWG	Terminal Dim.	Blade Fuse Dim.
Fuse Spec.	For Blade Fuses Used Only	6.3±0.5	19.1±0.5
Torque Rating	20in-lb (2.25Nm) max.	•	
Mounting Torque Rating	8in-lb (0.9Nm) max.		14.5±0.5 - 1
Temperature Rating	-20° C to 85° C	Circuit Diagram	







Material :

Cover: PC. (Transparent) Housing, Base: PBT. (Black) Push Button: POM. (White) Terminal: Tin. plating Copper

Notes :

 Rating 100A max. tested by 4 pcs. 25A load.

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.