




# Datasheet

Item no. 1588954, 1588881, 1588950, 1588904, 1588886, 1588953, 1588879, 1588880, 1588888, 1588952, 1588903, 1588955, 1588887, 1588951



Part No	Inductance L (µH)	f <sub>L</sub> (kHz)	Tol ± (%)	Rated DC Current (A)	DCR max (Ω)	Dimension (mm)			Fig.	Material
						D max	L max	d		
TC-77A-471M-00203	470	100	10,20	1	1.2	11	26	0.8	1	Ferrite
TC-77A-682M-00203	6800	10	10,20	0.3	9.6	11	26	0.8	1	Ferrite
TC-77A-5R6M-00203	5.6	1000	10,20	8	0.021	8	26	0.8	1	Ferrite
TC-77A-332M-00203	3300	10	10,20	0.5	4.8	11	26	0.8	1	Ferrite
TC-77A-3R9M-00203	3.9	1000	10,20	12	0.011	8	30	1	2	Ferrite
TC-77A-331M-00203	330	100	10,20	1.4	0.6	11	26	0.8	1	Ferrite
TC-77A-330M-00203	33	100	10,20	3.5	0.084	10	26	0.8	1	Ferrite
TC-77A-152M-00203	1500	10	10,20	0.7	2.4	11	26	0.8	1	Ferrite
TC-77A-151M-00203	150	100	10,20	1.8	0.36	11	26	0.8	1	Ferrite
TC-77A-150M-00203	15	100	10,20	4	0.06	9	26	0.8	1	Ferrite
TC-77A-102M-00203	1000	100	10,20	0.8	1.8	11	26	0.8	1	Ferrite
TC-77A-103M-00203	10000	10	10,20	0.3	14.4	11	26	0.8	1	Ferrite
TC-77A-101M-00203	100	100	10,20	2.5	0.18	11	26	0.8	1	Ferrite
TC-77A-100M-00203	10	1000	10,20	5	0.042	8	26	0.8	1	Ferrite



L(µH)	D	L	d
5.6, 10	8	26	0.8
15	9	26	0.8
33	10	26	0.8
68 -10,000	11	26	0.8