


Datasheet

Item no. 1589219, 1589090, 1589092, 1589224, 1589093, 1588989, 1589088, 1589091, 1589094, 1589217, 1589089, 1589222, 1589086, 1589220, 1589223, 1589218, 1589221, 1589087



Part No	Inductance (μ H)	fL (kHz)	Tol \pm (%)	DCR max (Ω)	Rated DC Current (A)	
					I _N	I _{SAT}
TC-07HCP-100M-50203	10	1 @ 0.25 V	20	0.040	2.6	5
TC-07HCP-101K-50203	100	1 @ 0.25 V	10,2	0.19	0.9	1.6
TC-07HCP-102K-50203	1000	1 @ 0.25 V	10,2	1.84	0.3	0.5
TC-07HCP-103K-50203	10000	1 @ 0.25 V	10,2	24	0.14	0.17
TC-07HCP-152K-50203	1500	1 @ 0.25 V	10,2	3.3	0.3	0.3
TC-07HCP-1R0M-50203	1.0	1 @ 0.25 V	20	0.007	7.5	10
TC-07HCP-220K-50203	22	1 @ 0.25 V	10,2	0.055	2.3	3.6
TC-07HCP-221K-50203	220	1 @ 0.25 V	10,2	0.38	0.64	1.2
TC-07HCP-222K-50203	2200	1 @ 0.25 V	10,2	5.30	0.19	0.25
TC-07HCP-330M-50203	33	1 @ 0.25 V	10,2	0.10	1.50	2.50
TC-07HCP-2R2M-50203	2.2	1 @ 0.25 V	20	0.01	6	8
TC-07HCP-331K-50203	330	1 @ 0.25 V	10,2	0.7	0.51	0.95
TC-07HCP-3R3M-50203	3.3	1 @ 0.25 V	20	0.013	5	6.3
TC-07HCP-470K-50203	47	1 @ 0.25 V	10,2	0.1	1.3	2.5
TC-07HCP-471K-50203	470	1 @ 0.25 V	10,2	0.89	0.43	0.8
TC-07HCP-4R7M-50203	4.7	1 @ 0.25 V	20	0.018	4	5.4
TC-07HCP-680K-50203	68	1 @ 0.25 V	10,2	0.14	1.1	2.1
TC-07HCP-6R8M-50203	6.8	1 @ 0.25 V	20	0.025	3.8	6.5

Material: Ferrite