

Datasheet

Item no. TC-K15PF5

ceramic capacitor NPO 15 pF ± 5% 100 V pitch 5.08 mm



Specification:

| | |
|-----------------------|----------------|
| Terminal | THR |
| Orientation | radial |
| Operating Voltage | ≤ 100 V |
| Operating Temperature | -25 °C - 85 °C |
| Capacitance | 15 pF |
| Material | NPO |
| Pitch | 5.08 mm |
| Tolerance | ± 5% |
| Type | ceramic |
| Packaging | bulk |

