

# Datasheet

Item no. TC-K22PF5

ceramic capacitor SL 22 pF ± 5% 100 V pitch 5.08 mm



## Specification:

Terminal	THR
Orientation	radial
Operating Voltage	≤ 100 V
Operating Temperature	-25 °C - 85 °C
Capacitance	22 pF
Material	SL
Pitch	5.08 mm
Tolerance	± 5%
Type	ceramic
Packaging	bulk

