

Datasheet

Item no. TC-K470PF5

ceramic capacitor Y5P 470 pF ± 10% 100 V pitch 5.08 mm



Specification:

Terminal	THR
Orientation	radial
Operating Voltage	≤ 100 V
Operating Temperature	-25 °C - 85 °C
Capacitance	470 pF
Material	Y5P
Pitch	5.08 mm
Tolerance	± 10%
Type	ceramic
Packaging	bulk

