

# Datasheet

Item no. TC-K22NF5

ceramic capacitor Z5V 22 nF -20% to +80V 100 V pitch 5.08 mm



## Specification:

Terminal	THR
Orientation	radial
Operating Voltage	≤ 100 V
Operating Temperature	-25 °C - 85 °C
Capacitance	22 nF
Material	Z5V
Pitch	5.08 mm
Tolerance	-20% to +80%
Type	ceramic
Packaging	bulk

