

Datasheet

Item no. TC-RKT330/2X12

toroidal transformer 330 VA 2 x 12 V 2 x 13750 mA



Specification:

Terminal	wire
Kind	toroidal transformer
Output Voltage	2 x 12 V
Output Current	≤ 2 x 13,7503 mA
Operating Temperature	≤ 40 °C
Input Voltage (Nom.)	230 V
Insulation Class	ta 40 / E
Power	≤ 330 VA
Efficiency	93 %

