

Datasheet

Item no. TC-K27PF2

ceramic capacitor NPO 27 pF ± 5% 100 V pitch 2.54 mm



Specification:

Terminal	THR
Orientation	radial
Operating Voltage	≤ 100 V
Operating Temperature	-25 °C - 85 °C
Capacitance	27 pF
Material	NPO
Pitch	2.54 mm
Tolerance	± 5%
Type	ceramic
Packaging	bulk

