

Datasheet

Item no. TC-K10NF5

ceramic capacitor Z5U 10 nF ±20% 100 V pitch 5.08 mm



Specification:

Terminal	THR
Orientation	radial
Operating Voltage	≤ 100 V
Operating Temperature	-25 °C - 85 °C
Capacitance	10 nF
Material	Z5U
Pitch	5.08 mm
Tolerance	±20%
Type	ceramic
Packaging	bulk

