

Datasheet

Item no. TC-K100NF5

ceramic capacitor Y5V 100 nF -20% to +80% 100 V pitch 5.08 mm



Specification:

Terminal	THR
Orientation	radial
Operating Voltage	$\leq 100\text{ V}$
Operating Temperature	$-25\text{ }^{\circ}\text{C} - 85\text{ }^{\circ}\text{C}$
Capacitance	100 nF
Material	Y5V
Pitch	5.08 mm
Tolerance	- 20% to +80%
Type	ceramic
Packaging	bulk

