

Datasheet

SPECIFICATIONS **TC-D28e-xxBT6 -G**




Material
Insulator : PBT, glass reinforced, rated UL 94V-0
Contact : Phosphor Bronze


Electrical
Current Rating : 1 Amp
Contact Resistance : 30 mΩ max.
Insulation Resistance : 3000 MΩ min.
Dielectric Withstanding Voltage : 500V AC for 1minute
Operating Temperature : -40˚C to +105˚C
▶Mating Suggestion: TC-D28b, TC-D28c series.






POSITION	A	B	C
4	5.84	3.81	7.16
6	8.38	6.35	9.70
8	10.92	8.89	12.24
10	13.46	11.43	14.78
12	16.00	13.97	17.32
14	18.54	16.51	19.86
16	21.08	19.05	22.40
18	23.62	21.59	24.94
20	26.16	24.13	27.48
22	28.70	26.67	30.02
24	31.24	29.21	32.56
26	33.78	31.75	35.10







RECOMMENDED P.C.B LAYOUT

How to order: TC-D28e - [1] - [2] - [3] - [4] - G(RoHS) Pitch 2,54mm x 1,5mm

1.NO. OF CONTACT	2.CONTACT MATERIAL	3.CONTACT PLATING	4.INSULATOR COLOR
04 06 08 10 12 14 16 18 20 22 24 26	**B: PHOSPHOR BRONZE**	**T: TIN PLATED** S: SELECTIVE G: GOLD FLASH A: 5u" INCH GOLD B: 10u" INCH GOLD C: 15u" INCH GOLD D: 30u" INCH GOLD	**6. RED**