



SPECIFICATIONS

1. Contact resistance: 20mΩ Max.
 2. Dielectric strength:
1,000VAC for 1 minute
 3. Insulation resistance:
100MΩ Min. at 500V DC
 4. Rating: 100VAC 2A
- All materials must be RoHS compliant.

