



Type Number..... 6032
Designation IEC..... CR 2032
System..... Li-Manganese dioxide/
 Organic Electrolyte

UL Recognition..... MH 13654 (N)
Nominal Voltage..... 3 V
Typical Capacity C..... 220 mAh
 Load 5.6 kOhm, at 20°C down to 2 V

Weight (approx.)..... 3 g
Volume..... 0,95 ccm

Temperature Ranges min max.
 Storage..... -55°C 70°C
 Discharge..... -20°C 70°C

Dimensions min max.
 Diameter (A) 19,7 20,0
 Height (B)..... 2,9 3,2
 Shoulder Diameter [E] 16,0

Segment..... Electronic

Main Applications..... Watch
 Photo
 Electronic

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0V
Continuous 24h/d, 7d/w	15000 Ω	Time:	1220 h
		Capacity:	220 mAh
		Energy:	610 mWh

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries