

Data Sheet

Spiral Tube (1593707, 1593708, 1593709, 1593710, 1593711, 1593195, 1593196, 1593197, 1593198, 1593199)



Threading Tool (1593215, 1593216, 1593217, 1593218, 1593219)



Data Sheet



Spiral Tube					Threading Tool		Material: P.P. Color: Black
B/N	D	T	W	Wrapping Range	B/N	D	
1593707 / 1593195	8	0.8	9	10	1593215	8	
1593708 / 1593196	15	0.8	13	16	1593216	15	
1593709 / 1593197	20	0.9	15	22	1593217	20	
1593710 / 1593198	25	1.3	18	27	1593218	25	
1593711 / 1593199	32	1.3	23	35	1593219	32	

Unit: mm

- Material: PP
- Color: Black
- Operating Temperature: 0 to 80°C
- Storage Temperature: 25 to 30 °C
- Application:
 1. Cut into suitable length, and use the special tool to wrap band the wire easily.
 2. Hold the topside of wire with installation tool, and draw down to wrap the wire immediately by easy and fast.
 3. This wire band designed to be easy off and re-usable, the tensile power will be remain after every wrap and peel.
- Tensile power: Easily applied and safety to protect cables and wire bundles from damage and electric harmless