

tesa® 4613

Duct tape for simple applications - available in white, black and grey

tesa® 4613 is a utility grade duct tape. It consists of a 27 mesh woven PET/cotton fabric backing coated with a natural rubber adhesive.

tesa® duct 4613 is a self adhesive tape with typical duct features for a wide range of applications.

Features:

- good adhesion even on rough surfaces
- easy to tear by hand
- water repellent
- flexible

Main Application

- Indoor and outdoor applications - even on rough surfaces
- Fastening of protection films
- Sealing of ducts
- Fixing, marking and packing
- Should not be used on painted surfaces

Technical Data

▪ Backing material	PE laminated cloth	▪ Elongation at break	18 %
▪ Total thickness	180 µm	▪ Tensile strength	30 N/cm
▪ Type of adhesive	natural rubber	▪ Temperature resistance (30 min)	95 °C
▪ Adhesion to steel	4.3 N/cm	▪ Mesh	27 count per square inch

Properties

- | | | | |
|-----------------------|-----|-----------------------|----|
| ▪ Hand tearability | ●●● | ▪ Abrasion resistance | ● |
| ▪ Straight tear edges | ●● | ▪ Water resistance | ●● |

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

For latest information on this product please visit <http://l.tesa.com/?ip=04613>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.