

tesa® 4316 PV3

Finely crêped paper masking tape for spray painting

tesa® 4316 is a finely crêped paper masking tape. The product is thin and flexible and, therefore, suitable for all general masking applications, as well as oven drying applications up to a temperature of 100 °C.

Main Application

The product is resistant to wet sanding. Paints and fillers ad-here well to the backing.

The material can be used on painted metal, rubber, glass and chrome parts.

Technical Data

▪ Backing material	slightly-creped paper	▪ Elongation at break	10 %
▪ Total thickness	140 µm	▪ Tensile strength	38 N/cm
▪ Type of adhesive	natural rubber	▪ Temperature resistance	100 °C
▪ Adhesion to steel	3.4 N/cm		

Properties

▪ Hand tearability	●●●●	▪ Sharp colour edge	●●●
▪ Easy to remove	yes	▪ Conformability	●●●
▪ Paint anchorage	●●●●		

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

For latest information on this product please visit <http://l.tesa.com/?ip=04316>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.