productinformation

tesa[®] 4962 Premium double-sided non-woven tape

tesa® 4962 is a double-sided tape consisting of a non-woven backing and a tackified acrylic adhesive.

tesa® 4962 features especially:

- High adhesion values on different substrates
- Excellent wetting (grabbing) power to rough surfaces
- Excellent temperature resistance performance

Main Application

Mounting of plastic and foam parts, heavy papers, textile and leather

Technical Data									
Backing materialColorTotal thickness	non-woven translucent 160 µm	Type of adhesiveElongation at breakTensile strength	tackified acrylic 3 % 8 N/cm						
Adhesion to									
 Steel (initial) ABS (initial) Aluminium (initial) PC (initial) PE (initial) PET (initial) PP (initial) PS (initial) PVC (initial) Steel (after 14 days) 	11.5 N/cm 11.0 N/cm 13.0 N/cm 6.5 N/cm 9.5 N/cm 8.5 N/cm 12.0 N/cm 11.0 N/cm	 ABS (after 14 days) Aluminium (after 14 days) PC (after 14 days) PC (covered side, after 14 days) PE (after 14 days) PET (after 14 days) PP (after 14 days) PS (after 14 days) PVC (after 14 days) 	12.0 N/cm 10.5 N/cm 12.4 N/cm 14.0 N/cm 10.5 N/cm 10.0 N/cm 13.0 N/cm 15.0 N/cm						

Properties

2	Temperature resistance short term Temperature resistance long term	200 °C 80 °C	2		er resistance hear resistance at 23°C	••
	Tack				hear resistance at 40°C	••
	Ageing resistance (UV)	••••		Static 5		
	Humidity resistance	••••				
•	Resistance to chemicals	•••				
Εv	aluation across relevant tesa [®] assortment	: •••• very good	•	e good	• e medium • low	

For latest information on this product please visit http://l.tesa.com/?ip=04962

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



en

tesa[®] 4962 Premium double-sided non-woven tape

Additional Information

Liner variants: PV0 brown glassine paper (71 µm)

According to VDA278 analysis, tesa 4962 does not contain any single substances restricted by the drafted GB regulations (China) as well as the indoor concentration guideline by Health, Labour and Welfare Ministry (Japan).

For latest information on this product please visit <u>http://l.tesa.com/?ip=04962</u>

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

