





Body Camera I DrivePro[™] Body 30

Transcend's DrivePro Body 30 is a feature-packed body camera designed specifically for public safety professionals. With a twelve-hour battery life, IP67 rated environmental sealing, military-grade shock resistance, and a pre-event buffer, the DrivePro Body 30 is always ready for action. The Sony image sensor, high-quality lens, automatic infrared illumination, and six-axis image stabilization guarantee clear, high-definition evidence collection. Paired with Transcend's DrivePro Body App for iOS and Android smartphones, users can easily control the DrivePro Body 30 and manage videos and photos on the device.





Supports Bluetooth and Wi-Fi connection

Up to 12 hours of battery life

- Sony high-sensitivity image sensor
- Six-axis image stabilization technology
- Pre-event buffering mode to save storage space and power consumption
- Up to 64GB capacious storage space
- Free download of DrivePro Body App

Note: 1. The DrivePro Body 30 was tested under controlled laboratory conditions and given a rating of IP67 under IEC standard 60529. Splash, water, and dust resistance are not permanent conditions and resistance may decrease as a result of normal wear. Product must be clean and dry before use. Liquid damage not covered under warranty.

2. US military drop-test standards based on MIL-STD-810G 516.6-Transit Drop Test.

Ordering Information

TS64GDPB30A



TS-DPD6N

Docking station is available for purchase.



Dimensions	95.9mm × 52.2mm × 27.6mm (3.78" x 2.06" x 1.09")
Weight	130g (4.59 oz)
Storage Capacity	64GB internal memory
Lens	F/2.0, 130° wide angle
Video Formats	H.264 (MOV: up to 1920x1080 30fps)
Operating Temperature	-20°C (-4°F) ~ 65°C (149°F)
Storage Temperature	-25°C (-13°F) ~ 70°C (158°F)
Certificates	CE, FCC, BSMI, NCC, MIC
Warranty	Two-year Limited Warranty