

Product fiche pursuant to Delegated Regulation (EU) no. 2019/2013

Televisions	Value	Units
SUPPLIER'S NAME OR TRADEMARK	TELEFUNKEN	
SUPPLIER'S MODEL IDENTIFIER	B32H440A weiss	
ENERGY EFFICIENCY CLASS FOR STANDARD DYNAMIC RANGE (SDR)	F	
ON-MODE POWER DEMAND FOR STANDARD DYNAMIC RANGE (SDR)	32	W
ENERGY EFFICIENCY CLASS (HDR)	N/A	
ON-MODE POWER DEMAND IN HIGH DYNAMIC RANGE (HDR) MODE	N/A	W
OFF-MODE POWER DEMAND	N/A	W
STANDBY MODE POWER DEMAND	0.5	W
NETWORKED STANDBY MODE POWER DEMAND	N/A	W
ELECTRONIC DISPLAY CATEGORY	Television	
SIZE RATIO	16:9	
SCREEN RESOLUTION (PIXELS)	1366 x 768	pixels
SCREEN DIAGONAL	80	cm
SCREEN DIAGONAL	32	inches
VISIBLE SCREEN AREA	2736,71	cm <sup>2</sup>
PANEL TECHNOLOGY USED	LCD-LED	
AUTOMATIC BRIGHTNESS CONTROL (ABC) AVAILABLE	No	
VOICE RECOGNITION SENSOR AVAILABLE	No	
ROOM PRESENCE SENSOR AVAILABLE	No	
IMAGE REFRESH FREQUENCY RATE	50	Hz
MINIMUM GUARANTEED AVAILABILITY OF SOFTWARE AND FIRMWARE UPDATES (UNTIL)		
MINIMUM GUARANTEED AVAILABILITY OF SPARE PARTS (UNTIL)		
MINIMUM GUARANTEED PRODUCT SUPPORT (UNTIL)		
POWER SUPPLY TYPE	INTERNAL	
<b>EXTERNAL STANDARDISED POWER SUPPLY (INCLUDED IN THE PRODUCT BOX)</b>		
INPUT VOLTAGE		V
OUTPUT VOLTAGE		V
<b>EXTERNAL STANDARDISED SUITABLE POWER SUPPLY (IF NOT INCLUDED IN THE PRODUCT BOX)</b>		
REQUIRED OUTPUT VOLTAGE		V
REQUIRED DELIVERED CURRENT		A
REQUIRED CURRENT FREQUENCY		Hz