



Einhell

HEATING

GCH 2000 W Convactor Heater

Item No.: 2338661

Ident No.: 11015

Bar Code: 4006825607543

The high-quality GCH 2000 W Convactor Heater is the perfect solution for energy-efficient heating between seasons or for fully heating smaller and average-sized rooms and comes in a superior design. Its X-shaped heating element allows it to heat up ultra-fast. The required room temperature can be easily set using two heat settings (1000 W/2000 W) and the thermostat (15 – 50°C).

Features

- X-shaped heating element allows the heater to heat up rapidly
- 2 heat settings (1000 W/2000 W)
- Thermostat adjustable from +15°C to +50°C
- Switch-off function with timer (1 – 23 hours)
- Touchscreen operation
- Remote control
- Face made from scratch-resistant glass
- Back-lit LCD panel
- Can be used as an upright heater or wall heater
- Overheating guard



Technical Data

- Max. heating power	2000 W
- Protection class	I
- Mains supply	230 V 50 Hz
- Unit dimensions	86 x 23 x 52.5 cm

Logistic Data

- Product weight	9.8 kg
- Gross weight single packaging	11.5 kg
- Pieces per export carton	1 Pieces
- Gross weight export carton	11.5 kg
- Dimensions single packaging	895 x 135 x 530 mm
- Dimensions export carton	900 x 135 x 525 mm
- Container quantity (20"/40"/40"HC)	410 845 990

