



G603 LIGHTSPEED™

Wireless Gaming Mouse



PLAY ADVANCED.

G603 is a next-generation gaming mouse designed for a wireless world. It has a rich set of advanced features and technologies to provide high performance for even the most demanding gamers. G603 is the first gaming mouse to feature the new HERO sensor which provides exceptional accuracy and precision, with a sensitivity of up to 12,000 DPI. At the same time, G603 delivers up to 10x the battery efficiency of prior generations. It also includes LIGHTSPEED wireless technology, which provides professional-grade wireless performance and unrivalled reliability—even surpassing many wired gaming mice.

WHAT'S IN THE BOX

- Wireless gaming mouse
- LIGHTSPEED™ USB receiver
- Receiver extender cable
- 2 AA batteries
- User documentation
- 2-year manufacturer's guarantee and full product support

FEATURES

- Next generation HERO™ sensor achieves zero smoothing and up to 12,000 DPI
- Exclusive LIGHTSPEED™ wireless technology delivers unrivalled performance
- Advanced Hi-Lo power management system
- Control multiple devices with dual connectivity



PACKAGE SPECIFICATIONS

	Primary pack	Master shipper carton
Part # EER2	910-005101	n/a
Bar code	5099206071926 (EAN-13)	50992060719211 (SCC-14)
Part # EWR2	910-005102	n/a
Bar code	5099206071933 (EAN-13)	50992060719310 (SCC-14)
Weight	219.3 gr	1048.9 gr
Length	13.6 cm	19.7 cm
Width	4.7 cm	15.4 cm
Height/depth	19.2 cm	20.8 cm
Volume	1.227 dm ³	0.006 m ³
1 primary pack	1	n/a
1 intermediate pack	0	n/a
1 master shipper carton	4	1
1 pallet EURO	1280	320
1 container 20 ft	19624	4906
1 container 40 ft	40524	10131
1 container 40 ft HQ	44208	11052

SYSTEM REQUIREMENTS

- LIGHTSPEED™: USB port and Windows® 7 or later, Mac OS X 10.12 or later, Chrome OS™, or Android™ 3.2 or later
- Bluetooth®: Bluetooth-enabled device with Windows® 8 or later, Mac OS X 10.10 or later, Chrome OS™, or Android™ 3.2 or later
- Internet access for Logitech Gaming Software

TECHNICAL SPECS

Tracking:

- Sensor: HERO™
- Resolution: 200-12,000 DPI
- Max. acceleration: tested at > 40 G*
- Max. speed: tested at > 400 IPS*

Responsiveness:

- USB data format: 16 bits/axis
- USB report rate in Hi mode: 1000 Hz (1 ms)
- USB report rate in Lo mode: 125 Hz (8 ms)
- Report rate in Bluetooth®: 125 Hz (8 ms)
- Microprocessor: 32-bit ARM

Durability:

- Main buttons: 20 million clicks with precision mechanical button tensioning
- Feet: tested at > 250-km range

Battery life:

- Hi mode: > 500 hours (non-stop gaming)
- Lo mode: > 18 months** (standard usage)

Physical specifications:

- Height: 124 mm
- Width: 68 mm
- Depth: 43 mm
- Weight: 88.9 g, mouse only/112.3 g, with 1 AA battery/135.7 g, with 2 AA batteries

* Tested on Logitech G240 Gaming Mouse Pad

** May vary based on user and computing conditions

