



Date	SYM	REVISION RECORD	AUTH	DR.	CK.
12/05/08	A	ADDED ROHS COMPLIANT	T.B.	B.S.	
08/01/14	B	UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	
03/03/17	C	DIM. 150.0 WAS 152.4 DIM. 5.0 WAS 3.18	T.B.	B.S.	
04/07/17	D	ADDED MOUNTING HOLES	T.B.	B.S.	
04/29/17	E	ADDED WIRES TO SIDE VIEW	T.B.	B.S.	



NOTES:


1. MATERIAL:

HOUSING : BLACK POLYPROPYLENE
 FLAMMABILITY RATING -UL94-HB, UL FILE NO. E216959
 TEMPERATURE RANGE: -10°C to +100°C
 WIRES: 26 AWG, UL1007, CSA-TR-64, 300V, 80°C
 RIVETS: BRASS, NICKEL PLATED.
 SPRING: SPRING STEEL, NICKEL PLATED.
 CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER
 EIA-540J000

MOUNTING INSTRUCTION:

USE 6-32 MACHINE SCREWS.
 ALSO ADHESIVES AND DOUBLE SIDED TAPES WORK WELL.

ROHS 2 COMPLIANT.

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735	Scale	Drawn By B.S.
			Approved By T.B.
decimal ±.5 (.020)	Title FOUR "D" CELL HOLDER WITH 6" WIRE LEADS		
Fractional ± .8 (.030)		Date 04/29/17	Drawing Number BH4DW
Angular ± 3°			