



10-Port USB Charging Station

76 W, 12 A USB Charging Dock with QC 2.0, Eight-bay Stand

Part No.: **180009**

Keep your portable devices fully powered and secure.

USB portable electronics place heavy demands on their batteries for power, but the Manhattan 10-Port USB Charging Station helps to keep your tablets, mobile phones, digital cameras and other devices charged and ready to go. The 10-Port USB Charging Station plugs into any standard wall outlet and offers rapid charging for your portable devices. (The first port supports Qualcomm QC 2.0 on devices with Snapdragon processors for 60% faster charging than conventional 1 A chargers, the next five ports charge at 1 A, and the last four ports support 2.4 A charging with Smart IC auto detect to find the best charge for your device.) Advanced built-in circuitry avoids overcharging and short-circuiting that can damage and reduce the life of batteries and devices. The Manhattan 10-Port USB Charging Station is perfect for home, school and office use. It features eight wide bays for securing most devices — with cases — while charging, keeping the countertop clean and clutter free.

Features:

- 10 port, front-mounted, USB wall charger for tablets, mobile phones and other portable devices
- Quick Charge (QC) 2.0 output on first port, 1 amp on next five ports and 2.4 amps on the last four ports
- QC 2.0 adaptive charging automatically adjusts power outputs between 2.4 A, 2 A or 1.5 A to fast charge your device
- Ports 2 through 6 charge five smartphones simultaneously with the 1 A power; ports 2-4 best for Android, ports 5-6 best for iPhone
- Almost twice as fast as 5W, ports 7-10 charge at 12W and feature a smart IC to auto-detect mobile device power requirements
- Eight device storage bays, up to 2 cm (0.75 in.) wide, with non-slip pads for secure, clutter-free use
- Advanced circuitry helps prevent overcharging, overheating and short-circuiting to increase your devices' battery life
- Sturdy, compact and heavy-duty; perfect for desktop charging for home, office, etc.
- Three-Year Warranty

Specifications:

Standards and Certifications

- CUL (power supply)
- RoHS2
- CE
- TUV (power supply)
- FCC

General

- Input voltage: input, 110 – 240 VAC, 50/60 Hz, max. 2 A

Port Type and Power Output

10 USB Type-A

- Port 1: (QC 2.0) 5 V / 2.4 A; 9 V / 2.1 A; 12 V / 1.5 A (output)
- Port 2-6: 5 V / 1 A (output); ports 2-4 best for Android, ports 5-6 best for iPhone
- Port 7-10: 5 V / 2.4 A / 12 W (output)

Physical

- Power button, LED power indicator
- Dimensions: 21 x 14 x 7 cm (8.3 x 5.5 x 2.8 in.)
- Divider dimensions (eight): 2 x 3.5 x 10 cm (0.8 x 1.4 x 3.9 in.)
- Weight: charger housing 0.43 kg (0.9 lbs.); with power adapter 0.8 kg (1.7 lbs.)
- Power cable and adapter: 2.7 m (8.9 ft.)
- Housing: ABS plastic

Operating Environment

- Operation temperature: 0 - 30°C (32 - 86°F)
- Storage temperature: -20 - 60°C (-4 - 140°F)
- Humidity (noncondensing): 0 - 90%

Package Contents

- 10-Port USB Charging Station
- Power adapter
- Power cable
- Quick Instruction Guide

