



RECEIVER

Full HD 1080p



FULL HD SAT Receiver

Free To Air (FTA)

Thanks to its small size, this SCHWAIGER® satellite receiver is ideal for camping or as a spare device at home. The receiver is suitable for operation at 12 V and in combination with an external memory device, the receiver has a Time Shift function. An integrated multimedia player allows for playback of music and pictures. The TV can be connected via a SCART or HDMI cable. The software update is done via USB. The TV can be connected via a SCART or HDMI cable. The software update via USB. Alter TextDieser SCHWAIGER® Satellitenreceiver ist wegen seiner kleinen Bauform perfekt für den Einsatz beim Camping oder auch als Zweitgerät für Ihr Zuhause geeignet. Der Receiver ist für den 12 V Betrieb geeignet und verfügt bei Anschluss

eines ext. Speichermediums über die Time Shift Funktion. Dank integriertem Multimediaoplayer können Fotos und Musik wiedergegeben werden. Neuer TextDieser SCHWAIGER® Satellitenreceiver ist wegen seiner kleinen Bauform perfekt für den Einsatz beim Camping oder auch als Zweitgerät für Ihr Zuhause geeignet. Der Receiver ist für den 12 V Betrieb geeignet und verfügt bei Anschluss eines ext. Speichermediums über die Time Shift Funktion. Dank eingebautem Mediaoplayer können Musik, Bilder und Filme wiedergegeben werden. Das Fernsehgerät kann über ein SCART oder HDMI-Kabel angeschlossen werden. Das Software-Update erfolgt über USB.

ARTICLE INFORMATION

Article Nr. DSR512HD
40040051026665



Last updated: 07.08.2017



FEATURES (DSR512HD)

- HDTV & SDTV SAT receiver
- suitable for LNB, motorized antenna or Unicable operation
- suitable for 12 volts operation with vehicle power cable
- multilingual screen menu
- 7-day Electronic Programme Guide (EPG) (dependent on channel)
- pre-programmed channel list (ASTRA 19.2°)
- video text (OSD) with subtitle function
- All Channels list and Favourite Channels list
- media player for music, pictures and movies integrated
- automatic channel scan (Fast Auto Scan)
- indication of signal strength and signal quality for best-possible antenna alignment
- automatic aspect ratio detection (4:3 <> 16:9)
- Games (Tetris, Othello, Sudoku)
- content: Receiver, 12 V car connection cable, power supply, remote control, 2x battery (1.5 V LR03 (AAA)), user manual

TECHNICAL DATA

Type of receiver	SAT (DVB-S2)
Display	4-digit LED display (7 segments)
Programme memory	3000
LNB IN (F-type)	1x (back)
LNB OUT (F-type)	1x (back)
USB 2.0 port	1x (front)
HDMI™ connection	1x (back)
Resolution	576i/576p/720p/1080i/Full HD 1080p
SCART connection	1x (back)
Digital sound output	1x (back) coaxial, S/PDIF
Control function	DiSEqC 1.0/1.1/1.2/1.3/USALS
Software update	via USB
Languages (Menu)	german/english/french/italian/spanish/turkish

Favourite channels list	8
Remote control	yes
Input frequency	950 - 2150 MHz
Power supply	100 - 240 V AC , 50/60 Hz 12 V DC , 1 A
Power consumption	in sleep mode < 0,5 W during operation < 6 W
Weight (set)	0,5 kg
Dimensions (width)	168 mm
Dimensions (height)	35 mm
Dimensions (depth)	95 mm
Guarantee	2-year guarantee (by law)
Packaging	carton

Last updated: 07.08.2017