

1 2 3 4 5 6 7 8 9 10 11 12 13 14

A

Nr. / No.	Beschreibung / Description
93884	CAT 6 PATCH U/UTP GRAU CCA 100m
93885	CAT 6 PATCH U/UTP GRAU CCA 305m
94964	CAT 6 PATCH U/UTP WEISS CCA 100m
94219	CAT 6 PATCH U/UTP WEISS CCA 305m

B

4x2x7/0.19±0.01 mm, AWG 24

Isolation/Insulation

C

D



E



F

Patchkabel

- Anschlüsse: ./.
- Standards: Cat 6 (250 MHz), TIA/EIA 568
- Wellenwiderstand: 100 Ohm
- Kabel: 4x2x7/0.19±0.01 mm, AWG 24
- Material:
 - Isolation: HDPE/PVC
 - Innenleiter: CCA
 - Füller: PE
 - Reißschnur: Nylon
- Brandschutzklasse: Eca
- Spannungsfestigk.: 1500 V~ 2s
- Konformität: CPR, RoHS

Patch cable

- Connectors: ./.
- Standards: Cat 6 (250 MHz), TIA/EIA 568
- Impedance: 100 Ohm
- Cable: 4x2x7/0.19±0.01 mm, AWG 24
- Material:
 - Insulation: HDPE/PVC
 - Inner cond.: CCA
 - Filler: PE
 - Rip cord: Nylon
- Fire protection class: Eca
- Dielectric strength: 1500 V~ 2s
- Conformity: CPR, RoHS

G

H

I

Änderungen

Datum	Name	gez.:	Datum	Name
		gepr.:	27.09.2017	tf
		Norm:		
		Änderungen vorbehalten / Subject to change		

Bezeichnung

CAT 6 PATCH U/UTP CCA



Blatt

Zeichnungs-Nr.:

von

J

1 2 3 4 5 6 7 8 9 10 11 12 13 14